

## Uhrenmeßschieber

### Ausführung:

DIN 862  
rostfreier Stahl  
vierfach Messung  
einschliesslich Etui



100-37

## Dial calipers



### Techn. data:

DIN 862  
stainless steel  
4 way measurements  
individually packed

## Pieds à coulisse à montre

### Applications:

DIN 862  
en inox  
4 fonctions de mesure  
emballés à l'unité

> mm <	 mm	 mm	No.	€	Calibr. ...K
150	0,02	40	100-35	33,10	6,80
200	0,02	50	100-36	44,25	13,00
150	0,01	40	100-37	37,30	6,80
200	0,01	50	100-38	49,40	13,00

## Digitale Meßschieber „Sylvac-System“

mit Opto-RS-Datenausgang

### Ausführung:

DIN 862  
rostfreier Stahl  
LCD-Anzeige 7,5 mm  
Feststellschraube  
vierfach Messung  
einschliesslich Etui



100-40

## Digital Caliper „Sylvac-System“

with data output Opto-RS

### Techn. data:



DIN 862  
stainless steel  
LCD-display 7,5 mm  
locking screw  
4 way measurements  
individually packed

## Pieds à coulisse digital

avec sortie de données Opto-RS

### Applications:



DIN 862  
en inox  
affichage LCD 7,5 mm  
4 fonctions de mesure  
emballés à l'unité

>mm<	 mm	 mm	No.	€	Calibr. ...K
150	0,01	40	100-40	83,80	6,80
200	0,01	50	100-41	104,20	13,00
Cable	Opto-RS 232C		100-43	72,10	
Battery	3 V-Lithium		100-44	4,80	

**Funktionen:** Ein/Aus, Null, hold  
mm/inch, ref.

**Features:** on/off, Zero, hold  
mm/inch, ref.

**Fonctions:** on/off, Zero, hold  
mm/inch, ref.

> mm < Messbereich  
 Ablesung mm / inch  
 Schnabellänge

Range  
Reading mm / inch  
Length of jaws

Capacité  
Lecture mm / inch  
Longueur des becs