

Electronic Professional Pliers

DURATOOL

The Best Pliers You'll Ever Use



New

- High quality ball bearing steel
- 63 - 65 Rockwell Hardness (HRC)
- 2-Component ESD Ergonomic handles, soft comfortable gripping surface, hard plastic core
- Dual leaf springs in blue steel
- Matched bearing rings to minimize metal-metal contact and friction

- Lap joint with screw to achieve a high level of strength and precision
- Static dissipative ($10^6 - 10^8 \Omega/\text{sq.}$), oil, grease and wear-resistant

531558

Mfrs. List No.	Jaw	Overall length		Order Code	Price Each		
		inch	mm		+	+	+
Long Snipe Nose							
D01013	Smooth	5.6"	143	169-6527	---	---	---
D01014	Serrated	5.6"	143	169-6528	---	---	---
Snipe Nose							
D01015	Smooth	5.2"	133	169-6529	---	---	---
D01016	Serrated	5.2"	133	169-6530	---	---	---
Flat Nose							
D01017	Smooth	5.2"	133	169-6532	---	---	---
Round Nose							
D01018	Smooth	5.2"	133	169-6533	---	---	---