

**HG 2300 E**

Powerful hot air gun for use with "Standard" hot air accessory attachments.

**Features**

- Fully electronic temperature and airflow control
- High-performance, long-life brushless motor
- Barrel shape for optimum stationary use

**Settings**

- Continuously adjustable air flow and temperature

**Maintenance**

- Easy-to-change heating element
- Easy-to change mains power cord



Easy-to-change heating element



Continuously adjustable



Easy-to change mains power cord



Suitable for push-on  
Suitable for push-on

**HG 2300 E**

Prod. No.

Length / dia. (at knock guard)

Voltage

Output

Temperature

Temperature control

Airflow rate

Air pressure

Air flow regulation

**350314**

355 mm / 100 mm

230 V / 50 Hz  
(other voltages also available)

2300 W

25 - 600° C

continuous

600 l / min. max.

3000 Pa

continuously variable

delivery nozzle	suitable for "Standard" attachments (34 mm dia.)
Motor life	approx. 5000 hrs.
Heater life	approx. 800 hrs.
Mains power cord	H07 RN-F 2 x 1 length 2.5 m
Weight	850 g
	Subject to technical modifications



[print](#) [close](#)