

**A Series IP-44, IP-55, IP-56 Junction Boxes**

With Stepped Glands and Press Fit Lids - IP-44

Reference	Description
A1	∅ 65 x 35 (round)
A2	∅ 80 x 35 (round)
A3	□ 80 x 80 x 40

With Smooth Walls and Grey Screw on Lids - IP-56

Reference	Description
AS05	120 x 80 x 60
AS15	100 x 100 x 60
AS25	150 x 100 x 60
AS35	190 x 140 x 70
AS45	240 x 190 x 90
AS55*	300 x 220 x 120
AS65*	380 x 300 x 120

\*Lid fixing by means of plastic screws; box complete of plastic hinge.

With Smooth Walls and Transparent Screw On Lids - IP-56

Reference	Description
AS25T	150 x 100 x 60
AS35T	190 x 140 x 70
AS45T	240 x 190 x 90
AS55T*	300 x 220 x 120
AS65T*	380 x 300 x 120

\*Lid fixing by means of plastic screws; box complete of plastic hinge.

High Lid With Smooth Walls and Grey Screw On Lids - IP-55

Reference	Description
ASH15	110 x 110 x 112
ASH25	150 x 110 x 150
ASH35	150 x 150 x 150
ASH45	220 x 150 x 150
ASH55	300 x 220 x 150

\*Lid fixing by means of plastic screws; box complete of plastic hinge.

High Transparent Lid With Smooth Walls and Grey Screw On Lids - IP-55

Reference	Description
ASH15T	110 x 110 x 112
ASH25T	150 x 110 x 150
ASH35T	150 x 150 x 150
ASH45T	220 x 150 x 150
ASH55T	300 x 220 x 150

Metal Plate

Reference	Description
PB1	for boxes AS3 - 35 - 35T
PB2	for boxes AS4 - 45 - 45T
PB3	for boxes AS5 - 55 - 55T
PB4	for boxes AS6 - 65 - 65T
PB5	for boxes ASH15 - ASH15T
PB6	for boxes ASH25 - ASH25T
PB7	for boxes ASH35 - ASH35T
PB8	for boxes ASH45 - ASH45T
PB9	for boxes ASH55 - ASH55T



**C Series IP-40, IP-55 Distribution Boards**

Surface Mounting Without Door - IP-40

Reference	Description	Dimensions
CT2	1-2 pole	51 x 130 x 60
CT4	3-4 pole	88 x 130 x 60

Surface Mounting - Complete With Transparent Door - IP40

Reference	Description	Dimensions
CT5PT	4 + 1 smooth sides	144 x 168 x 94
CT8PT	8 smooth sides	215 x 168 x 94
CT12PT	12 + 1 smooth sides	283 x 168 x 94
CT24PT	24 smooth sides	256 x 326 x 101

Wall Mounting Enclosures - IP-55

Reference	Description	Dimensions
CT3G	3 pole	83 x 175 x 114
CT5G	5 pole	125 x 175 x 114
CT8G	8 pole	215 x 175 x 114
CT12G	12+1 pole	287 x 200 x 122

Wall Mounting Distribution Boards - IP-55

Reference	Description	Dimensions
CT12NS	12 way	285 x 250 x 136
CT24NS	24 way	285 x 375 x 136

Distribution Boards With Provision For CEE Sockets - IP-65

Reference	Description	Dimensions
CT24GL	24 way	285 x 375 x 136
CT36GL	36 way	285 x 500 x 136

Terminal Bar Supports In Polycarbonate (960°C G.W. Test)

Reference	Description	Pack Qty
CTR3	For CT5G - CT5SG - CT5GT	10
CTR4	For CT8G - CT8SG - CT8GT - CT12G CT12SG - CT12SG1 - CT12GT	10
CTR5	For CT3G	10

Terminal Bar Supports In Polycarbonate (960°C G.W. Test)

Reference	Description	Pack Qty
CTR6	For CT24L - CT36L	10
CTR9	For CT5-CT5PT-CT5PT/C ( 1 piece steel + 1 SUM 1)	10
CTR10	For CT8-CT8PT-CT8PT/C ( 1 piece steel + 1 SUM 1)	10
CTR11	For CT12-PT-PT/C ( 1 piece steel + 1 SUM 1)	10
CTR12	For CT24/36-PT-PO-PT/C-PO/C ( 1 piece steel + 1 SUM 2)	10

