

**L754 MINIATURE CERAMIC FUSE LINKS**





These size 00 (15.9mm x 4.7mm), sand filled fuse links have a high rupturing capacity and a category duty of 250V a.c. or 250V d.c. (Maximum prospective overload 4000A at 0.4pf and 250Va.c. and 230 V d.c. Time constant 0.004s.)

- MINIMUM LIFE:** 1,000 hours at rated current at temperatures up to 35°C. 1,000 hours continuous at 80% of rated current at temperatures beyond 35°C to 85°C.
- TEMPERATURE RANGE:** -60°C to +85°C
- MARKING:** Body marked with rating and approved versions carry the Joint Services' reference number
- WEIGHT:** 0.85g

**ORDERING REFERENCE: L754/CURRENT RATING IN AMPERES**

**AVAILABLE IN : 50mA, 100mA, \*250mA, \*500mA, \*1A, \*2A**  
\* Qualification Approved



BLP reserve the right to change without prior notice the information contained within this leaflet

BLP Components Ltd., Exning Road, Newmarket, Suffolk, CB8 0AX, England  
Tel: +44 (0)1638 665161 Fax: +44 (0)1638 660718 email: sales@blpcomp.com <http://www.blpcomp.com>