





























DS-Serie

Modell				Bestell Nr.	
	Außendurchmesser mm	Innendurchmesser mm	Länge mm		
DS110		1,9	0,7	18	5 13 510 99
DS111		2,5	0,7	18	5 13 511 99
DS112		2,3	1,0	18	5 13 512 99
DS113		2,5	1,2	18	5 13 513 99
DS114		3,3	1,8	18	5 13 514 99
DS115		1,9	0,7	24,5	5 13 515 99
DS116		2,7	1,2	24,5	5 13 516 99
DS117		2,9	1,5	18	5 13 550 99
DS118		1,5	0,7	18	5 13 551 99
DS110 HM		1,9	0,7	18	5 13 532 99
DS112 HM		2,3	1,0	18	5 13 533 99
DS113 HM		2,5	1,2	18	5 13 530 99
Saugnadel DS119		1,9	0,7	26	5 13 527 99
DS120 zum Reinigen von SMD-pads		2,5	1,1	15,5	5 13 552 99
Temp. Meßspitze		3,3	0,55	18	5 24 749 99

DS-Serie (UNC)

Modell				Bestell Nr.	
	Außendurchmesser	Innendurchmesser	Länge		
DS110 UNC		1,15mm/0,060"	0,63mm/0,025"	19mm/0,75"	0151352099
DS111 UNC		2,29mm/0,090"	0,63mm/0,025"	19mm/0,75"	0151352199
DS112 UNC		1,93mm/0,076"	0,91mm/0,036"	19mm/0,75"	0151352299
DS113 UNC		2,39mm/0,094"	1,14mm/0,045"	19mm/0,75"	0151352399
DS114 UNC		3,17mm/0,125"	1,80mm/0,071"	19mm/0,75"	0151352499
DS115 UNC		1,52mm/0,060"	0,63mm/0,025"	24mm/0,98"	0151352599
DS116 UNC		2,49mm/0,098"	1,14mm/0,045"	25mm/0,98"	0151352699