

SPECIAL ESD/EGB ELECTRONIC PLIERS

Box joint 
 Double leaf spring
 Bright steel-polished
 With conductive black hand-guard



CUTTING PLIERS

No.	Length		Finish	Cutting capacity mm Ø		Weight g
	mm	inches		Soft wire	Hard wire	

Side cutters

with slim, rounded head, available with or without side face

3-601-13	120	4 3/4	with side face	1.0	0.4	70
3-602-13	120	4 3/4	without side face	1.0	-	70

Side cutters

with slim, pointed head, available with or without side face

3-603-13	120	4 3/4	with side face	0.8	-	65
3-604-13	120	4 3/4	without side face	0.8	-	65

End cutters

with angular tips and oblique cutting edge,
 for flush cutting, for soft wire only

3-606-13	120	4 3/4	without side face	0.4	-	55
----------	-----	-------	-------------------	-----	---	----

ROUND, FLAT AND SNIPE NOSE PLIERS

No.	article	Length		Finish	Weight g
		mm	inches		
3-631-13	Round nose pliers	120	4 3/4	plain jaws	55
3-632-13	Flat nose pliers	120	4 3/4	plain jaws	55
3-633-13	Snipe nose pliers	120	4 3/4	plain jaws	55
3-634-13	Snipe nose pliers, angular	120	4 3/4	plain jaws	55

SETS OF ELECTRONIC PLIERS

3-650 Set of conductive pliers, 5 pieces

in a practical table support from antistatic material

Tool set:

Weight: 320 g

No.	Description of individual tools
3-601-13	Side cutters , 120 mm, for hard wire up to 0.4 mm, for soft wire up to 1.0 mm
3-631-13	Round nose pliers , 120 mm, plain jaws
3-632-13	Flat nose pliers , 120 mm, plain jaws
3-633-13	Snipe nose pliers , 120 mm, plain jaws
3-634-13	Snipe nose pliers , angular, 120 mm, plain jaws

3-630 Set of conductive pliers, 3 pieces

in a wallet of recycable nylon

Tool set:

Weight: 240 g

No.	Description of individual tools
3-601-13	Side cutters , 120 mm, for hard wire up to 0.4 mm, for soft wire up to 1.0 mm
3-632-13	Flat nose pliers , 120 mm, plain jaws
3-633-13	Snipe nose pliers , 120 mm, plain jaws



3-601-13




3-603-13



3-606-13




3-631-13



3-632-13



3-633-13



3-634-13

