

ESD/EGB SPECIAL-TOOLS



with slim, ergonomically formed handles from black, **conductive** plastic. The centring head guarantees a precise working without exhaustion.

Blade: chrome vanadium, hardened over its full length, chrome-plated, black tip,

Handle: impact-resistant, **conductive** black plastic, electrostatic discharge according to DIN EN 1000 15/1

TORX-screwdrivers



No.	Size	Blade length mm	for metric thread	Handle length mm	Weight
6-659	T 4	50	M 1.4-1.6	90	12 g
6-661	T 5	50	M 1.6-2	90	12 g
6-662	T 6	50	M 2	90	16 g
6-663	T 7	50	M 2.5	90	13 g
6-664	T 8	60	M 2.5	90	14 g
6-665 L	T 9	60	M 3	90	19 g
6-666 L	T 10	60	M 3-3.5	90	20 g

from size T 9 with bore-hole in the tip



6-660 6-piece TORX-screwdriver-set,

in a practical support from **conductive** material

Contents: 6 TORX-screwdrivers No. 6-661, 6-662, 6-663, 6-664, 6-665, 6-666

Weight: 163 g

Wrench keys



No.	A/F mm	Blade length mm	Handle length mm	Weight
6-631	0.7	50	90	11 g
6-632	0.9	50	90	12 g
6-633	1.3	50	90	12 g
6-634	1.5	50	90	12 g
6-635	2.0	60	90	12 g
6-636	2.5	60	90	14 g

6-630 6-piece wrench key set

in a practical support from **conductive** material

Contents: 6 wrench keys No. 6-631, 6-632, 6-633, 6-634, 6-635, 6-636

Weight: 142 g

Socket wrenches



No.	A/F mm	Blade length mm	Handle length mm	Weight
6-611	1.5	70	90	14 g
6-612	2.0	70	90	14 g
6-613	2.5	70	90	14 g
6-614	3.0	70	90	14 g
6-615	3.2	70	90	14 g
6-616	3.5	70	90	15 g
6-617	4.0	70	90	15 g
6-618	4.5	70	90	16 g
6-619	5.0	70	90	16 g
6-621	5.5	70	90	20 g

6-610 6-piece socket wrenches

in a practical support from **conductive** material

Contents: 6 Socket wrenches No. 6-612, 6-614, 6-617, 6-618, 6-619, 6-621

Weight: 156 g

