


Wire Strippers

A range of tools for accurately stripping insulation from wire and cables, to save time and money.



**3657 Maxi Waterpump pliers**

DIN ISO 8976

Item Number	↔	Ø
T-3657 250	250mm 10"	50mm 2"
T-3657 300	300mm 12"	65mm 2 1/2"

Patented design plier which has fine push button adjustment to 11 positions, this ensures fast working. Extra large gripping capacity of over 50mm<sup>2</sup>. Ideal for almost any application. Manufactured from quality chrome vanadium steel and box jointed design provide strength and durability. Slim head and jaws allow work in confined spaces. Contoured, antislip, long handles provide a tool which is comfortable and easy to use.



**3659A Waterpump pliers**

DIN ISO 8976

Item Number	↔	Ø
T-3659A 175	175mm 7"	30mm 1 1/8"
T-3659A 240	250mm 10"	32mm 2 1/4"
T-3659A 300	300mm 12"	38mm 1 1/2"
T-3659A 400	400mm 16"	64mm 2 1/2"

Manufactured from hot drop forged chrome vanadium steel, oil hardened and tempered to specified levels. Box jointed construction gives accuracy and long life. Slim head design for use in confined spaces. Parallelogram shaped jaws grip well on smooth and irregular surfaces. 7 position adjustment. Built in stop prevents finger nipping. Black stove enamel finish with PVC coated handles.

C-K waterpump pliers are constructed using box joints as opposed to laid on joints. This means the pivot is supported on both sides of the jaw. While this is more complicated to manufacture, the end product is stronger and will last longer.



**3755 Precision fibre stripper**

Item Number	Ø
T3755 018	0.18mm
T3755 025	0.25mm
T3755 060	0.60mm
T3755 080	0.80mm

For fibre optic cable.



**3757 Precision wire stripper**

Item Number	Ø
330009	0.12 - 0.40mm
330013	0.25 - 0.80mm
330011	0.30 - 1.00mm

Adjustable to six diameters - for PVC, teflon and similar.



**3756 Precision fibre stripper**

Item Number	Ø
T3756 20	0.20mm
T3756 25	0.25mm
T3756 30	0.30mm
T3756 40	0.40mm
T3756 50	0.50mm
T3756 60	0.60mm
T3756 80	0.80mm
T3756 100	1mm

For PVC, teflon and similar.

The range of precision wire strippers is designed for use on delicate wire for nick free stripping. Operation is simple - wire is passed through the hole and the handle squeezed.



**3330 Cable stripper**  
kabifix

Item Number	Ø
430004	6 - 28mm, 1 tube

Item Number	i
385041	5 spare blade

Dual Purpose wire stripper and plastic tube cutting tool. Cuts and removes insulation from cables, solid conductors and standardised wire. Cuts plastic tubes up to 1.0". Safe and fast stripping of cable insulation up to strong outer sheaths. Automatic change from circular to longitudinal cut. Adjustable cutting depth and replaceable hardened blade, all ensure a fast/easy cut.



**3759 Precision wire stripper & cutter**

Item Number	Ø
T3759	0.25, 0.30, 0.40, 0.50, 0.60, 0.80mm

Adjustable length stop with 1.5mm scale. Precision metal cutting and stripping blade, hardened. Integrated wire cutter for copper wires up to 0.8mm Ø. Easily adjustable to 6 wire diameters in graduations of 0.25, 0.30, 0.40, 0.50, 0.60 & 0.80mm.