

Product Data Sheet

T6500 Lightning Plus



Safety Products



Description: New generation safety and sports spectacle with face-fitting curve and soft nose piece for maximum comfort. Equipped with straight sports temples and soft temple tips. Engineered to adapt RX-prescription insert.

Materials:

Lens	– Curve 9 based polycarbonate lens 4A-coated; Anti-scratch, Anti-mist, Anti-static and Anti-UV Colours: Clear, Smoke, Amber
Temples	– Material : Polycarbonate
Colour	- Black, blue, bronze, silver.
Nose piece	– Clear, Soft PVC
Screws	– Stainless steel

Weight: 31 gr.

Standards:

Frame	– EN166	N	F
Lens	– EN166	N	1F
	– EN170 UV 2-1,2	N	1F (Clear, Amber)
	– EN172 5-3,1	N	1F (Smoke)

Technical Performance

Impact resistance	– 6mm steel ball at 45m/s.
Visible light transmission	– 92% minimum
UV absorption	– 100% up to 390nm
Heat resistance	– up to 80°C
Abrasion resistance	– conforms to EN166 requirement

Application: Protects against impacts from flying particles of increased robustness in accordance with cited standards.

Options:

- RX Insert for prescription lenses
- Cases :204508, 204512, 204513
- Cords :204522, 204520, 608010, 608011 and 608012
- Nose piece :208590
- Cleaning :LCS2, T1025T, 10204

Packaging: Individual polyethylene bags in boxes of 10

artnr. 9062xx

