

Premium Enhanced Cat5e UTP Patch Cables


Part No: 2965 - (Length) + (Colour) see chart

Available in 15 colours, the extensive range of patch cables are designed for Cat.5e networking requirements. Each cable is manufactured to the highest standards and specification from stranded Cat.5E cable and High Quality RJ45 plugs. They are fully tested and fitted with short bodied connectors and integral strain relief boots.



Features & Benefits


- Designed for advanced bandwidth frequency systems & increased network speeds.
- Manufactured using quality component parts: Connectors: 50micron gold RJ45 plugs
- Cable: UL approved Cat.5e enhanced 24 AWG stranded cable
- To reduce crosstalk, short-bodied connectors maintain speed & data integrity on moulded assemblies
- Wide choice of 15 colours - helping to identify cable paths at a glance
- Ex-stock delivery on all 14 different lengths
- Pin 1 to 1 wiring configuration
- Tested for purpose, ideal for current network patching requirements.



Premium Enhanced Cat5e UTP Patch Cables

Part No: 2965 - (Length) + (Colour) see chart






Part Number Chart

Length	Beige 	Blue 	Blue 	Brown 	Gold 
0.3 Metre	2965-0.3	2965-0.3B	2965-0.3BK	2965-0.3BR	2965-0.3AU
0.5 Metre	2965-0.5	2965-0.5B	2965-0.5BK	2965-0.5BR	2965-0.5AU
0.75 Metre	2965-0.75	2965-0.75B	2965-0.75BK	2965-0.75BR	2965-0.75AU
1 Metre	2965-1	2965-1B	2965-1BK	2965-1BR	2965-1AU
1.25 Metre	2965-1.25	2965-1.25B	2965-1.25BK	2965-1.25BR	2965-1.25AU
1.5 Metre	2965-1.5	2965-1.5B	2965-1.5BK	2965-1.5BR	2965-1.5AU
2 Metre	2965-2	2965-2B	2965-2BK	2965-2BR	2965-2AU
3 Metre	2965-3	2965-3B	2965-3BK	2965-3BR	2965-3AU
4 Metre	2965-4	2965-4B	2965-4BK	2965-4BR	2965-4AU
5 Metre	2965-5	2965-5B	2965-5BK	2965-5BR	2965-5AU
8 Metre	2965-8	2965-8B	2965-8BK	2965-8BR	2965-8AU
10 Metre	2965-10	2965-10B	2965-10BK	2965-10BR	2965-10AU
15 Metre	2965-15	2965-15B	2965-15BK	2965-15BR	2965-15AU
20 Metre	2965-20	2965-20B	2965-20BK	2965-20BR	2965-20AU
30 Metre	2965-30	2965-30B	2965-30BK	2965-30BR	2965-30AU

Premium Enhanced Cat5e UTP Patch Cables

Part No: 2965 - (Length) + (Colour) see chart

Part Number Chart

Length	Green 	Grey 	Transparent 	Orange 	Pink 
0.3 Metre	2965-0.3G	2965-0.3GY	2965-0.3IM	2965-0.3RG	2965-0.3PK
0.5 Metre	2965-0.5G	2965-0.5GY	2965-0.5IM	2965-0.5RG	2965-0.5PK
0.75 Metre	2965-0.75G	2965-0.75GY	2965-0.75IM	2965-0.75RG	2965-0.75PK
1 Metre	2965-1G	2965-1GY	2965-1IM	2965-1RG	2965-1PK
1.25 Metre	2965-1.25G	2965-1.25GY	2965-1.25IM	2965-1.25RG	2965-1.25PK
1.5 Metre	2965-1.5G	2965-1.5GY	2965-1.5IM	2965-1.5RG	2965-1.5PK
2 Metre	2965-2G	2965-2GY	2965-2IM	2965-2RG	2965-2PK
3 Metre	2965-3G	2965-3GY	2965-3IM	2965-3RG	2965-3PK
4 Metre	2965-4G	2965-4GY	2965-4IM	2965-4RG	2965-4PK
5 Metre	2965-5G	2965-5GY	2965-5IM	2965-5RG	2965-5PK
8 Metre	2965-8G	2965-8GY	2965-8IM	2965-8RG	2965-8PK
10 Metre	2965-10G	2965-10GY	2965-10IM	2965-10RG	2965-10PK
15 Metre	2965-15G	2965-15GY	2965-15IM	2965-15RG	2965-15PK
20 Metre	2965-20G	2965-20GY	2965-20IM	2965-20RG	2965-20PK
30 Metre	2965-30G	2965-30GY	2965-30IM	2965-30RG	2965-30PK

VIDEK

Premium Enhanced Cat5e UTP Patch Cables

Part No: 2965 - (Length) + (Colour) see chart

Part Number Chart

Length	Purple 	Red 	Silver 	White 	Yellow 
0.3 Metre	2965-0.3PR	2965-0.3R	2965-0.3AG	2965-0.3W	2965-0.3Y
0.5 Metre	2965-0.5PR	2965-0.5R	2965-0.5AG	2965-0.5W	2965-0.5Y
0.75 Metre	2965-0.75PR	2965-0.75R	2965-0.75AG	2965-0.75W	2965-0.75Y
1 Metre	2965-1PR	2965-1R	2965-1AG	2965-1W	2965-1Y
1.25 Metre	2965-1.25PR	2965-1.25R	2965-1.25AG	2965-1.25W	2965-1.25Y
1.5 Metre	2965-1.5PR	2965-1.5R	2965-1.5AG	2965-1.5W	2965-1.5Y
2 Metre	2965-2PR	2965-2R	2965-2AG	2965-2W	2965-2Y
3 Metre	2965-3PR	2965-3R	2965-3AG	2965-3W	2965-3Y
4 Metre	2965-4PR	2965-4R	2965-4AG	2965-4W	2965-4Y
5 Metre	2965-5PR	2965-5R	2965-5AG	2965-5W	2965-5Y
8 Metre	2965-8PR	2965-8R	2965-8AG	2965-8W	2965-8Y
10 Metre	2965-10PR	2965-10R	2965-10AG	2965-10W	2965-10Y
15 Metre	2965-15PR	2965-15R	2965-15AG	2965-15W	2965-15Y
20 Metre	2965-20PR	2965-20R	2965-20AG	2965-20W	2965-20Y
30 Metre	2965-30PR	2965-30R	2965-30AG	2965-30W	2965-30Y