

Cat5e Patch Cables


Booted Cat5e UTP Patch Cables

Part No: 2961 - (Length) + (Colour) see chart

These high quality Cat.5E patch cables provide excellent value for money. All cables are manufactured with high quality RJ45 connectors.

Features & Benefits

- Extremely competitively priced range of patch cables, fully tested
- High quality patch cables with updated specification
- Manufactured using quality piece parts
- Connectors: 50 micron gold RJ45 plugs
- Cable: EIA/TIA TSB40-A, Cat.5 stranded 24 AWG UL approved cable
- Certified to 100 MHz requirements
- Suitable for all current data, voice and ISDN patching
- All lengths held in stock for immediate despatch
- Seven colours available for easy identification







Cat5e Patch Cables

Booted Cat5e UTP Patch Cables

Part No: 2961 - (Length) + (Colour) see chart

Part Number Chart




Length	Beige 	Grey 	Black 	Blue 	Green 
0.5 Metre	2961-0.5	2961-0.5GY	2961-0.5BK	2961-0.5B	2961-0.5G
1 Metre	2961-1	2961-1GY	2961-1BK	2961-1B	2961-1G
1.5 Metre	2961-1.5	2961-1.5GY	2961-1.5BK	2961-1.5B	2961-1.5G
2 Metre	2961-2	2961-2GY	2961-2BK	2961-2B	2961-2G
3 Metre	2961-3	2961-3GY	2961-3BK	2961-3B	2961-3G
5 Metre	2961-5	2961-5GY	2961-5BK	2961-5B	2961-5G
8 Metre	2961-8	2961-8GY	2961-8BK	2961-8B	2961-8G
10 Metre	2961-10	2961-10GY	2961-10BK	2961-10B	2961-10G
15 Metre	2961-15	2961-15GY	2961-15BK	2961-15B	2961-15G
20 Metre	2961-20	2961-20GY	2961-20BK	2961-20B	2961-20G
30 Metre	2961-30	2961-30GY	2961-30BK	2961-30B	2961-30G
50 Metre	2961-50	-	-	-	-

Cat5e Patch Cables

Booted Cat5e UTP Patch Cables

Part No: 2961 - (Length) + (Colour) see chart

Part Number Chart

Length	Red 	White 	Yellow 	Orange 	Purple 
0.5 Metre	2961-0.5R	2961-0.5W	2961-0.5Y	2961-0.5RG	2961-0.5PR
1 Metre	2961-1R	2961-1W	2961-1Y	2961-1RG	2961-1PR
1.5 Metre	2961-1.5R	2961-1.5W	2961-1.5Y	2961-1.5RG	2961-1.5PR
2 Metre	2961-2R	2961-2W	2961-2Y	2961-2RG	2961-2PR
3 Metre	2961-3R	2961-3W	2961-3Y	2961-3RG	2961-3PR
5 Metre	2961-5R	2961-5W	2961-5Y	2961-5RG	2961-5PR
8 Metre	2961-8R	2961-8W	2961-8Y	2961-8RG	2961-8PR
10 Metre	2961-10R	2961-10W	2961-10Y	2961-10RG	2961-10PR
15 Metre	2961-15R	2961-15W	2961-15Y	2961-15RG	2961-15PR
20 Metre	2961-20R	2961-20W	2961-20Y	2961-20RG	2961-20PR
30 Metre	2961-30R	2961-30W	2961-30Y	2961-30RG	2961-30PR
50 Metre	-	2961-50W	-	-	-