


## Shielded Cat5e FTP Patch Cables Cat.5e STP Patch Cables

Part No: 1962 - (Length) + (Colour) see chart

The STP cables are manufactured using stranded core, foil screened Cat.5e cable and a shielded plug fitted with matching strain relief boot. All cables are available from stock in the lengths listed below. Custom made cables are available upon request. For full details of this service please contact our sales department.

### Features & Benefits

- Manufactured using quality components
- Connectors: 50 micron gold, shielded RJ45 plugs
- Cable: EIA/TIA T568-A, Cat.5e stranded, foil shielded UL approved cable
- Wired to 258A specification using a quality shielded plug and strain relief boot
- Suitable for all current data, voice and ISDN patching
- Ex-stock availability on lengths listed
- Choice of 6 colours for easy recognition
- Contact our Sales Department for our cable labelling service available on short lead time, price quoted is per label, normally 2 labels required per cable one at each end









# Shielded Cat5e FTP Patch Cables

## Cat.5e STP Patch Cables

Part No: 1962 - (Length) + (Colour) see chart

### Part Number Chart

| Length    | Beige  | Black  | Blue  | Green  | Red  | Yellow  |
|-----------|---|---|--|---|---|--|
| 0.3 Metre | 1962-0.3  | -   | -  | -   | -   | -  |
| 0.5 Metre | 1962-0.5  | 1962-0.5BK  | 1962-0.5B  | 1962-0.5G   | 1962-0.5R   | 1962-0.5Y  |
| 1 Metre   | 1962-1  | 1962-1BK  | 1962-1B  | 1962-1G   | 1962-1R   | 1962-1Y  |
| 1.5 Metre | 1962-1.5  | -   | 1962-1.5B  | -   | 1962-1.5R   | -  |
| 2 Metre   | 1962-2  | 1962-2BK  | 1962-2B  | 1962-2G   | 1962-2R   | 1962-2Y  |
| 3 Metre   | 1962-3  | 1962-3BK  | 1962-3B  | 1962-3G   | 1962-3R   | 1962-3Y  |
| 5 Metre   | 1962-5  | 1962-5BK  | 1962-5B  | 1962-5G   | 1962-5R   | 1962-5Y  |
| 8 Metre   | 1962-8  | -   | -  | -   | -   | -  |
| 10 Metre  | 1962-10   | 1962-10BK   | 1962-10B   | 1962-10G  | 1962-10R  | 1962-10Y   |
| 15 Metre  | 1962-15   | -   | -  | -   | -   | -  |
| 20 Metre  | 1962-20   | -   | -  | -   | -   | -  |
| 25 Metre  | 1962-25   | -   | -  | -   | -   | -  |
| 30 Metre  | -   | -   | -  | -   | -   | -  |
| 50 Metre  | 1962-50   | -   | -  | -   | -   | -  |
| 100 Metre | 1962-100  | -   | -  | -   | -   | -  |