

Hand Protection



NITRILE / NEOPRENE CHEMICAL RESISTANT GLOVES



CHEMSOFT

Blue, special formulated Nitrile rubber gloves with a textured finish to provide extra grip in wet or dry conditions. Ideal for use with certain solvents and chemicals. They offer stretch and flexibility of natural rubber, but provide the solvent and chemical resistance of Nitrile rubber. Length 33 cm.



art.no.	thickness	description	sizes
CS113B*	0,28 mm	unflocked	7S, 8M, 9L, 10XL, 11XXL
CS153B*	0,38 mm	flocklined	7S, 8M, 9L, 10XL, 11XXL
Standards	EN420, EN388 (4101), EN374, EN421, CE Category Complex Design		
Packaging	12 pairs per bag, 144 pairs per case		



NITRI GUARD PLUS

Specially designed for handling inorganic acids and alkalis. Ideal for use in the chemical industry and other applications requiring flexibility and dexterity. Flock lined to give improved user comfort.



art.no.	thickness	description	length	EN388
LA102G*	0,28 mm (11 mil)	unflocked	33 cm	4001
LA132G*	0,38 mm (15 mil)	flocklined	33 cm	4001
LA142G*	0,38 mm (15 mil)	unflocked	33 cm	4001
LA172G*	0,43 mm (17 mil)	flocklined	33 cm	4001
LA225G*	0,56 mm (22 mil)	unflocked	38 cm	4002
LA258G*	0,63 mm (25 mil)	unflocked	45 cm	4102
Standards	EN420.2003, EN388.2003, EN374.2003 CE Category Complex design			
Packaging	12 pairs per pack, 144 pairs per case, LA225G & LA258G, 72 pairs			
* = in accordance with FDA regulations				



NITRI KNIT

Blue Nitrile supported and liquid proof gauntlet. Unique textured finish provides a sure grip on oily, wet or dry objects. Tough Nitrile outer layer offers good resistance to cuts, snags and abrasion as well as providing good chemical resistance to a wide range of chemicals.



art.no.	description	sizes
NK803	30 cm length	7S, 8M, 9L, 10XL
Standards	EN420, EN388 (4121), EN374. CE Category Complex Design	
Packaging	12 pairs per bag, 144 per case	

NITRI KNIT PLUS

The new generation of chemical resistant gloves. In accordance with EN 374.2003 for chemical protection. With a seamless knitted liner for high comfort as no seams will hinder the user. Nitril coating for good mechanical protection with bisque finish for good grip. Furthermore protection against contact heat according to EN407.2003 up to a least 100 degrees, so ideal also for handling hot liquids.



art.no.	length	sizes
NK850	30 cm	7S, 8M, 9L, 10XL, 11XXL
Standards	EN420.2003, EN388.2003, EN374.2003, EN407.2004 CE category: complex design	
Packaging	12 pairs per polybag, 72 pairs per case	



NEO TASK GLOVES & GAUNTLETS

Heavy duty Neoprene gloves with smooth and rough finish in lengths from 300 - 450 mm depending on the degree of protection required.



art.no.	description	size
T1041	smooth finish and knitted wrist	11XXL
T1241	smooth, length 30 cm, (12")	11XXL
T1241WG	same but rough	11XXL
T1441	smooth, length 35 cm (14")	11XXL
T1441WG	same but rough	11XXL
T1841	smooth, length 45 cm (18")	11XXL
T1841WG	same but rough	11XXL
Standards	EN420.2003, EN388.2003, EN374.2003, CE Category Complex Design	
Packaging	12 pairs / bag, 72 pairs / case; T1841+T1841WG: 6 pairs / bag, 36 pairs / case	

CUT & SEWN NITRILE GLOVES



WORKNIT

Heavy duty slip on cut and sewn glove with a black dash or black striped back. The cotton jersey fabric is coated with high quality brown Nitrile rubber. The heavy weight fleece lining provides superior cushioning for tough jobs, which gives good absorption of perspiration for greater comfort.



art. no.	description	sizes
85/8721	safety cuff and black dash back men's sizes	9L, 10XL
85/3721	slip on type with black dash back, men's sizes	8M, 9L, 10XL
85/3729	slip on type with cotton striped back, men's sizes	8M, 9L, 10XL, 11XXL
85/5729	winter version: slip on type with cotton striped back	8M, 9L, 10XL
Standards	EN420, EN388 (3111), CE Category Intermediate risks	
	85/5729, EN 388 (1212) EN511 (11X)	
Packaging	12 pairs per bag, 144 pairs per case, 85/5729, 36 pairs per case	