

Product Data Sheet

NORTH

Safety Products

Product image:



Product name: A2B2

Part number: A168096

Characteristics

Standard: EN 141
Thread connection: EN 148
Pressure drop: 105 Pa
Weight: 235 g
Dimensions: \varnothing 107 x 65mm
Colour: Silver

Materials

Housing: Coated aluminium
Adsorbent: Activated carbon, AB-type
Sealing caps: Polyethylene

Storage conditions

Temperature: -30°C to +70°C
Relative Humidity: < 90%
Expiry date: See canister bottom

Usage: Organic gases and vapours; Anorganic gases and vapours

Limitations for use:

Do not use where the oxygen level in the atmosphere is less than 17%

Do not use with organic gases and vapours with a boiling point below 65°C

Applications: Full Face and Half Masks with EN148 connection, Compact Air (Plus).

Note:

The maximum mass of filter(s) designated to be used directly connected to a half mask is 300gr. (EN143).

The maximum mass of filter(s) designated to be used directly connected to a full face mask is 500gr. (EN143).

Packaging: 4 filters in a carton./4 cartons in a box./ 16 filters in a box
Dimensions /Weight : 48x 24.5x 23.5cm / 04.8kg