

# KERN DA5-3

Comfortable testing of screw tops, e.g. bottles



## Packaging & shipping


Delivery:	24 h
Dimensions packaging (WxDxH):	345 x 295 x 90 mm
Gross weight:	3,700 kg
Net weight:	2,911 kg
Shipping method:	Parcel service
UN number:	3496

## Construction

Casing material:	Metal lacquered
Dimensions (WxDxH):	100 x 160 x 250 mm
Dimensions housing (WxDxH):	250 x 160 x 60 mm

## Piktogramme

### STANDARD



### OPTION



## Measuring system

Measuring capacity [Max]:	5 Nm
Overload protection (of [Max]):	120 %
Precision (of [Max]):	0,500 %
Readability [d]:	0,001 Nm
Weighing units:	Nm. kgf/cm. kgf/m. in/lbs. ft/lbs

## Functions

Function to set limits:	yes
Peak function:	yes

## Environmental conditions

Maximum operating temperature:	35 °C
Minimum ambient temperature:	15 °C

## Power supply

Charging time:	14 h
Input voltage:	100 V - 240 V
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH
Operating time (Backlight off):	18 h

## Services (optional)

Factory calibration certificate:	961-120
----------------------------------	---------

## Category

Brand:	Sauter
Category:	Torque