

KERN DB20-3

Convenient way to test the torque of tools



Packaging & shipping


Delivery:	24 h
Dimensions packaging (WxDxH):	350 x 295 x 30 mm
Gross weight:	4,393 kg
Net weight:	3,320 kg
Shipping method:	Parcel service
UN number:	3496

Construction

Casing material:	Metal lacquered
Dimensions (WxDxH):	200 x 100 x 50 mm
Dimensions device (WxDxH):	200 x 100 x 50 mm
Dimensions housing (WxDxH):	200 x 100 x 50 mm
Overall dimensions mounted (WxDxH):	200 x 100 x 50 mm

Piktogramme

STANDARD



OPTION



Measuring system

Measuring capacity [Max]:	20 Nm
Overload protection (of [Max]):	120 %
Precision (of [Max]):	0,500 %
Readability [d]:	0,005 Nm
Weighing units:	Nm. kgf/cm. kgf/m. in/lbs. ft/lbs

Functions

Function to set limits:	yes
Peak function:	yes

Environmental conditions

Maximum operating temperature:	35 °C
Minimum ambient temperature:	15 °C

Power supply

Charging time:	14 h
Input voltage:	100 V - 240 V
Mains adapter:	Mains adapter external
Mains adapter/adaptor included:	EURO CH
Operating time (Backlight off):	18 h

Services (optional)

Factory calibration certificate:	961-120
----------------------------------	---------

Category

Brand:	Sauter
Category:	Torque