



Size	T-3 1/4 WB T10
Socket Type	Twistlock
Contact Type	Double contact
Bulb Type	T10
Rating	12V-24V
Circuit Thickness	1,5mm - 1 or 2 faces
Socket Colour	Black
Lamp replaceable	Yes
Body Material	Polyamide with glass fibre
Contact Material	Spring steel
Comments	
ROHS Status	Yes

Drawn : HOK	Ch'd : HOK	Datasheet : 7121	Print date : 04/09/06
Revision : 1.0	Revision date : 2005-09-06	Name : HOK	Scale : 2 : 1