



- Eliminates screws
- Secures wires to any pre-drilled panel
- Can be installed in any panel thickness
- Low profile design keeps bundle close to mounting surface where overhead space is limited

Easy to Install:

- Push rivet in pre-drilled panel hole
- Use **PANDUIT** Nylon Rivet Installation Tool (TNR) or hammer to drive the pin flush to the base to secure the mount
- Attach wires to the mount with a cable tie

Part Number:	KIMS-H366-C2
Product Family:	Low Profile Mounts – Push Rivet Applied
Product Line:	Push/Tree Barb
Product Line:	Screw/Rivet Applied
RoHS Compliancy Status:	Compliant
Part Description:	Push Rivet Low Profile Cable Tie Mount
Product Type:	Cable Tie Mounts - Screw / Rivet Mounted
Material:	Nylon 6.6
Color:	Red
UL Recognized:	E136577
Height (In.):	.12
Height (mm):	3.0
Length (In.):	.74
Length (mm):	18.7
Width (In.):	.49
Width (mm):	12.4
CE Compliant:	CT-ACC4 / 10.96
Environment:	Indoors
Flammability Rating:	UL94 V-2
Hole Diameter (In.):	.144

