



- Eliminates screws
- Secures wires to any pre-drilled panel
- Can be installed in any panel thickness
- Low profile design keeps bundle close to mounting surface where overhead space is limited

Easy to Install:

- Push rivet in pre-drilled panel hole
- Use **PANDUIT** Nylon Rivet Installation Tool (TNR) or hammer to drive the pin flush to the base to secure the mount
- Attach wires to the mount with a cable tie

Part Number: KIMS-H500-C4
Product Family: Low Profile Mounts – Push Rivet Applied
Product Line: Push/Tree Barb

Product Line: Screw/Rivet Applied

RoHS Compliancy Status: Compliant

Part Description: Push Rivet Low Profile Cable Tie Mount

Product Type: Cable Tie Mounts - Screw / Rivet Mounted

Material: Nylon 6.6

Color: Yellow

UL Recognized: E136577

Height (In.): .12

Height (mm): 3.0

Length (In.): .74

Length (mm): 18.7

Width (In.): .49

Width (mm): 12.4

CE Compliant: CT-ACC4 / 10.96

Environment: Indoors

Flammability Rating: UL94 V-2

Hole Diameter (In.): .196

Hole Diameter (mm): 5.0

