



Low profile and versatile these screw-installed mounts can be ideal for applications where space is limited. Designed for four-way cable tie insertion this mount can be mounted in-line or perpendicular to the wire bundle.

- 4-way cable tie entry makes part orientation fast and easy
- Install with a screw or rivet for a strong, secure installation
- Small overall size allows use where space is limited

‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Ties.

Part Number: TA1S8-C  
Product Family: Tie Anchor Mounts – Screw Applied  
Product Line: Screw/Rivet Applied

RoHS Compliancy Status: Compliant

Part Description: Cable Tie Mount - Screw Applied

Product Type: Cable Tie Mounts - Screw / Rivet Mounted

Material: Nylon 6.6

Color: Natural

UL Recognized: E136577

Height (In.): .20

Height (mm): 5.1

Length (In.): .38

Length (mm): 9.5

Width (In.): .75

Width (mm): 19.0

CE Compliant: CT-ACC4 / 10.96

Environment: Indoors

Flammability Rating: UL94 V-2

Hole Diameter (In.): .17

Hole Diameter (mm): 4.3

Metric Screw Size: M4

