



- Durable nylon cable clamps

Part Number: CCH12-S10-C  
Product Family: Fixed Diameter Cable Clamps  
Product Line: Screw/Rivet Applied

RoHS Compliancy Status: Compliant

Part Description: Heavy Duty Fixed Diameter Cable Clamp

Product Type: Mounting Device

Material: Nylon 6.6

Color: Natural

UL Recognized: E136577

Diameter (In.): .20

Diameter (mm): 5.1

Width (In.): .50

Width (mm): 12.7

|                              |                |
|------------------------------|----------------|
| Bundle Offset (mm):          | 9.1            |
| Bundle Offset (In.):         | .36            |
| Environment:                 | Indoors        |
| Flammability Rating:         | UL94 V-2       |
| Hole Diameter (In.):         | .20            |
| Hole Diameter (mm):          | 5.1            |
| Max. Bundle Diameter (In.):  | .12            |
| Max. Bundle Diameter (mm):   | 3.1            |
| Metric Screw Size:           | M5             |
| Mounting Hole Distance (mm): | 9.1            |
| Mounting Method:             | #10 (M5) Screw |
| Screw Size:                  | #10 (M5)       |
| Std. Pkg. UOM:               | PK             |
| Type Of Application:         | Heavy Duty     |
| UOM:                         | PC             |
| Std. Pkg. Qty.:              | 100            |
| Min. Order Qty.:             | 100            |