



System consists of harness board springs and spring holders to hold wire ends taut. When harness is removed from board wires simply pull out from spring. Each SHH Spring Holder is supplied with (1) rigid wire piece to hold the spring laterally and two #8 (M4), 2.0" (50.8) hex head wood screws. Two sizes of spring holders are available for use with PBSC1 and PBSC6 springs.

Part Number: PBSC6-X
Product Family: Spring Wire Breakout System
Product Line: Harness Board Accessories

RoHS Compliancy Status: RoHS directive is not applicable

Part Description: Spring Wire Breakout System

Product Type: Harness Board Accessories

Material: Steel

Height (mm): 11.2

Length (In.): 6.00

Length (mm): 152.4

Breakout Component: PBSC Spring Wire Breakout

Breakout Length (In.): 6

Breakout Length (mm): 152.4

Environment: Indoors

Head Height (In.): .44

Material Thickness (In.): 0.035

Material Thickness (mm): 0.9

Mounting Method: SHH3 Spring Holder

Std. Pkg. UOM: PK

UOM: PC

Std. Pkg. Qty.: 10

Min. Order Qty.: 10