



- Clamp ties are used to attach a bundle to another surface such as a control panel wall or ceiling using another fastener.
- The design allows for bundling before or after screwing clamp in place.

Part Number: PLC2S-S10-C0  
Product Family: *Pan-Ty*® Clamp Ties - Weather Resistant  
Product Line: Clamp Cable Ties

RoHS Compliancy Status: Compliant

Part Description: Clamp Tie, 7.9", Standard cross section

Product Type: Cable Ties

Material: Weather Resistant Nylon 6.6

Color: Black

CSA Certified: Yes

UL Listed (File #E56854): No

UL Recognized (File #E56854): Yes

Length (In.): 7.9

Length (mm): 201

Width (In.):	.190
Width (mm):	4.8
Boss Height (In.):	.160
Boss Height (mm):	4.1
Boss Width (In.):	.373
Boss Width (mm):	9.5
CE Compliant:	Yes
Cross Section:	Standard
Locking Style:	Locking
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	1.84
Max. Bundle Diameter (mm):	47
Max. Continuous Use Temperature:	185°F (85°C)
Metric Screw Size:	M5
Min. Loop Tensile Strength (Lbs.):	50
Min. Loop Tensile Strength (N):	222
Nominal Hole Diameter (In.):	.200
Nominal Hole Diameter (mm):	5.1
Screw Size:	#10

Std. Pkg. UOM:	PK
Thickness (In.):	.047
Thickness (mm):	1.2
Tool:	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100