



- Used to fasten and identify bundles at the same time.
- Can be marked with *PANDUIT* Marker Pens.
- Can be custom imprinted with text, symbols or trademarks using *PANDUIT* Custom Hot Stamping Service.
- Can be marked with Computer Printable Labels.

Part Number:	PL2M2S-L0
Product Family:	<i>Pan-Ty</i> ® Marker & Flag Ties - Weather Resistant
Product Line:	Marker Cable Ties
RoHS Compliancy Status:	Compliant
Part Description:	Marker Tie, Wrap, 7.4", Standard cross section
Product Type:	Cable Ties
Material:	Weather Resistant Nylon 6.6
Color:	Black
CSA Certified:	Yes
UL Listed (File #E56854):	No
UL Recognized (File #E56854):	Yes
Length (In.):	7.4

Length (mm):	188
Width (In.):	.185
Width (mm):	4.7
CE Compliant:	Yes
Cross Section:	Standard
Head Height (In.):	.220
Head Height (mm):	5.6
Head Width (In.):	.320
Head Width (mm):	8.1
Locking Style:	Locking
Marker Type:	Wrap
Marker Write-On Area (In.):	.87 x 1.07
Marker Write-On Area (mm):	22.1 x 27.2
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	1.75
Max. Bundle Diameter (mm):	45
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	50
Min. Loop Tensile Strength (N):	222

Std. Pkg. UOM:	PK
Thickness (In.):	.052
Thickness (mm):	1.3
Tool:	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2
UOM:	PC
Std. Pkg. Qty.:	50
Min. Order Qty.:	50