



- Marker Ties fasten and provide a surface to identify bundles at the same time.
- Can be marked with *PANDUIT* Marker Pens
- Can be custom imprinted with text, symbols or trademarks using *PANDUIT* Custom Hot Stamping Service.
- Can be marked with Computer Printable Labels.

Part Number:	PLM2S-C4Y
Product Family:	<i>Pan-Ty</i> ® Marker & Flag Ties - Colors
Product Line:	Marker Cable Ties
RoHS Compliancy Status:	Compliant
Note:	PLM2S-C4Y replaces PLM2S-C4
Part Description:	Marker Tie, Wrap, 7.4", Standard cross section
Product Type:	Cable Ties
Material:	Nylon 6.6
Color:	Yellow
CSA Certified:	Yes
Mil. Std. Part Number:	MS3368-1-4A
UL Listed (File #E56854):	No

UL Recognized (File #E56854):	Yes
Length (In.):	7.4
Length (mm):	188
Width (In.):	.185
Width (mm):	4.7
CE Compliant:	Yes
Cross Section:	Standard
Head Height (In.):	.220
Head Height (mm):	5.6
Head Width (In.):	.320
Head Width (mm):	8.1
Locking Style:	Locking
Marker Type:	Wrap
Marker Write-On Area (In.):	.44 x .87
Marker Write-On Area (mm):	11.1 x 22.1
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	1.75
Max. Bundle Diameter (mm):	45
Max. Continuous Use Temperature:	185°F (85°C)

Min. Loop Tensile Strength (Lbs.): 50

Min. Loop Tensile Strength (N): 222

Std. Pkg. UOM: PK

Thickness (In.): .052

Thickness (mm): 1.3

Tool: GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH,
PPTS, STS2, STH2

UOM: PC

Std. Pkg. Qty.: 100

Min. Order Qty.: 100