



- For identifying and coding telephone and fiber optic cable.
- Replaces costly and cumbersome lead marking tags.
- Lightweight and easy to install.
- Can be used as wrap-around or flag marker.
- Can also be used in underground identification applications.
- Can be marked using *PANDUIT* Custom Hot Stamping service.

Part Number:	CM4S-L8
Product Family:	Polyethylene Cable Marker Strap
Product Line:	Marker Cable Ties
RoHS Compliancy Status:	Compliant
Part Description:	Cable Marker Strap, 15.3", Standard cross section
Product Type:	Cable Ties
Material:	Polyethylene
Color:	Gray
CSA Certified:	No
UL Listed (File #E56854):	No
UL Recognized (File #E56854):	No

Length (In.):	15.3
Length (mm):	387
Width (In.):	.750
Width (mm):	19.1
CE Compliant:	Yes
Cross Section:	Standard
Locking Style:	Locking
Marker Length (In.):	3.88
Marker Length (mm):	98.5
Marker Type:	Flag/Wrap
Marker Width (In.):	1.50
Marker Width (mm):	38.1
Marker Write-On Area (In.):	1.50 x 2.62
Marker Write-On Area (mm):	38.1 x 66.5
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	4.38
Max. Bundle Diameter (mm):	111
Max. Continuous Use Temperature:	185°F (85°C)
Std. Pkg. UOM:	PK

Thickness (In.):	.033
Thickness (mm):	.84
Tool:	Hand Installed Only
UOM:	PC
Std. Pkg. Qty.:	50
Min. Order Qty.:	50