

Product information

00 19 57

Set of Circlip Pliers

4 parts

- Four common Precision Circlip Pliers for highest requirements
- Dimensions, open (L x H): 315 x 275 mm
- Tool roll made of hard-wearing polyester fabric
- With practical, adjustable quick release fastener







General

| | |
|-------------|---------------|
| Article No. | 00 19 57 |
| EAN | 4003773050056 |
| Weight | 725 g |
| Dimensions | 111 x 65 mm |
| Reach | no |
| RohS | no |

Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040301 |
| ETIM 5.0 | EC000149 |
| ETIM 6.0 | EC000149 |
| proficl@ss 6.0 | EAD130c001 |
| UNSPSC 13.1 | 27112126 |

Content

| | |
|----------|--|
| 48 11 J1 | 1 x Precision Circlip Pliers for internal circlips in bore holes (Ø 12 - 25 mm)  |
| 48 11 J2 | 1 x Precision Circlip Pliers for internal circlips in bore holes (Ø 19 - 60 mm)  |
| 49 11 A1 | 1 x Precision Circlip Pliers for external circlips on shafts (Ø 10 – 25 mm)  |
| 49 11 A2 | 1 x Precision Circlip Pliers for external circlips on shafts (Ø 19 – 60 mm)  |

technical change and errors excepted