

## Product information

# 12 40 200

## Self-Adjusting Insulation Stripper



- For thin ribbon cables up to 10.0 mm width in a single pass
- For single, multiple and fine stranded conductors with plastic or rubber insulation
- Adapts automatically to the respective cable cross-section; prevents damage to the conductor
- Cutting depth can be adjusted for different insulation materials
- With wire cutter for copper and aluminium wires, multiple stranded up to 10 mm<sup>2</sup> and single stranded up to 6 mm<sup>2</sup>
- Smoothly operating mechanism
- Stripping blades and clamping jaws easily replaceable
- Low weight
- Body: plastic, fibreglass-reinforced
- Blade: special tool steel, oil-hardened

AAA



### General

Article No.	12 40 200
EAN	4003773026662
Weight	202 g
Dimensions	200 x 95 x 21 mm
Reach	yes
RohS	no

### Technical details

Stripping capacities in square millimetres	0.03 — 10.0 mm <sup>2</sup>
Length stop	3 – 18 mm
AWG	32 — 8

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27111510


### Spare Parts

12 49 01	1 pair of spare blades for 12 40 200,
12 49 02	1 pair of spare clamping jaws for 12 40 200,
12 49 03	Spare length stop for 12 40 200,
12 49 04	Torsion spring for 12 40/50 200,
12 49 05	Coil spring in the head for 12 40/50 200,

technical change and errors excepted



12 40 200: Adjustable length stop



12 40 200: Precise stripping prevents damage to the conductor