

## Product information

# 78 03 125 ESD

## Electronic Super Knips® ESD


DIN ISO 9654 DIN EN 61 340-5



- Cutting edge hardness approx. 54 HRC
- INOX tool steel
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Ground, very sharp cutting edges without bevel
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Precisely shaped tips cut wires close to a surface from Ø 0.2 mm
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter



General	
Article No.	78 03 125 ESD
EAN	4003773025146
Head	polished
Handles	with multi-component grips
Weight	55 g
Dimensions	125 x 61 x 13 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
Reach	no
RohS	no
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 1.0 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 1.6 mm
Jaw length (B)	9 mm
Jaw thickness (joint) (D)	7.5 mm
Head width (A)	13.5 mm
ESD	yes



<b>Classification</b>	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112149

*technical change and errors excepted*

