


Product information

97 49 15

- Application: Flag terminals and non-insulated, open plug type connectors (6.3 mm connector width) 1.25-2.5 + 3.0-6.0 mm²

Crimping die

For plug connectors and non-insulated open plug-type connectors



General

| | |
|-------------|---------------|
| Article No. | 97 49 15 |
| EAN | 4003773043164 |
| Weight | 56 g |
| Dimensions | 50 x 17 mm |
| Reach | yes |
| RohS | no |

Technical details



| | |
|--------------------------------|--|
| Applications | for plug connectors and angled spade connectors according to DIN 46346 Form A (1.5 - 2.5 mm ²) 2 + 3 crimping die: for non-insulated, open lug connectors (straight version) according to DIN 46247 (2.5 – 6 mm ²) |
| Capacity in square millimetres | 1.25 — 2.5 / 3 — 6 mm ² |
| Number of crimping positions | 2 |



| Classification | |
|-----------------------|------------|
| eCl@ss 5.1.4 | 21040301 |
| ETIM 5.0 | EC000168 |
| ETIM 6.0 | EC000168 |
| proficl@ss 6.0 | AAA946c003 |
| UNSPSC 13.1 | 27112820 |

technical change and errors excepted