



## SKINDICHT® ZS-M

Brass fitting




### Application


Hexagonal converter with metric connecting thread and PG inner thread. The converters enable the use of glands with PG threads in metric housing holes.

### Special Feature

With long metric connecting thread.

### Technical Data

 Material:  
Messing vernickelt

 Note:  
Massblatt auf  
Anfrage

Part-Number	Outside thread M	Inside thread PG	Wrench size mm	Outer thread length mm	PU pieces
For a quotation please click on a part number					
<b>SKINDICHT® ZS-M</b>					
5210 4330	12 x 1,5	7	14	5	100
5210 4340	16 x 1,5	9	18	5	100
5210 4010	16 x 1,5	11	20	5	100
5210 4360	20 x 1,5	11	22	6	100
5210 4370	20 x 1,5	13,5	22	6	100
5210 4380	20 x 1,5	16	24	6	50
5210 4400	25 x 1,5	21	30	7	50
5210 4410	32 x 1,5	29	40	8	25
5210 4420	40 x 1,5	36	50	8	10
5210 4430	50 x 1,5	42	57	9	10
5210 4440	63 x 1,5	48	66	10	10
<b>SKINDICHT® ZS-M-XL</b>					
5210 4335	12 x 1,5	7	14	10	100
5210 4345	16 x 1,5	9	18	10	100
5210 4365	20 x 1,5	11	22	10	100
5210 4375	20 x 1,5	13,5	22	10	100
5210 4385	20 x 1,5	16	24	10	50

