

EKDMGN011A-KIT:

Metal Alloy Power Inductors for DC-DC Converter Circuit:

NO .	QTY	MANUFACTURER'S PART NUMBER	Product Description	DESCRIPTION
1	10	DFE322512F-R47M=P2	Fixed IND SMD	Fixed IND 0.47uH 6700mA NONAUTO
2	10	DFE322512F-1R0M=P2	Fixed IND SMD	Fixed IND 1uH 4800mA NONAUTO
3	10	DFE322512F-1R5M=P2	Fixed IND SMD	Fixed IND 1.5uH 3900mA NONAUTO
4	10	DFE322512F-2R2M=P2	Fixed IND SMD	Fixed IND 2.2uH 3400mA NONAUTO
5	10	DFE322512F-3R3M=P2	Fixed IND SMD	Fixed IND 3.3uH 2600mA NONAUTO
6	10	DFE322512F-4R7M=P2	Fixed IND SMD	Fixed IND 4.7uH 2300mA NONAUTO
7	10	DFE322512F-100M=P2	Fixed IND SMD	Fixed IND 10uH 1700mA NONAUTO
8	10	DFE252010F-100M=P2	Fixed IND SMD	Fixed IND 10uH 1300mA NONAUTO
9	10	DFE252010F-1R0M=P2	Fixed IND SMD	Fixed IND 1uH 4100mA NONAUTO
10	10	DFE252010F-1R5M=P2	Fixed IND SMD	Fixed IND 1.5uH 3400mA NONAUTO
11	10	DFE252010F-2R2M=P2	Fixed IND SMD	Fixed IND 2.2uH 3100mA NONAUTO
12	10	DFE252010F-3R3M=P2	Fixed IND SMD	Fixed IND 3.3uH 2200mA NONAUTO
13	10	DFE252010F-4R7M=P2	Fixed IND SMD	Fixed IND 4.7uH 1900mA NONAUTO
14	10	DFE252010F-R33M=P2	Fixed IND SMD	Fixed IND 0.33uH 6800mA NONAUTO
15	10	DFE252010F-R47M=P2	Fixed IND SMD	Fixed IND 0.47uH 6000mA NONAUTO
16	10	DFE252012F-100M=P2	Fixed IND SMD	Fixed IND 10uH 1400mA NONAUTO
17	10	DFE252012F-1R0M=P2	Fixed IND SMD	Fixed IND 1uH 4700mA NONAUTO
18	10	DFE252012F-1R5M=P2	Fixed IND SMD	Fixed IND 1.5uH 3800mA NONAUTO
19	10	DFE252012F-2R2M=P2	Fixed IND SMD	Fixed IND 2.2uH 3300mA NONAUTO
20	10	DFE252012F-3R3M=P2	Fixed IND SMD	Fixed IND 3.3uH 2500mA NONAUTO
21	10	DFE252012F-4R7M=P2	Fixed IND SMD	Fixed IND 4.7uH 2100mA NONAUTO
22	10	DFE252012F-R33M=P2	Fixed IND SMD	Fixed IND 0.33uH 7600mA NONAUTO
23	10	DFE252012F-R47M=P2	Fixed IND SMD	Fixed IND 0.47uH 6700mA NONAUTO
24	10	DFE201612E-R24M=P2	Fixed IND SMD	Fixed IND 0.24uH 6600mA NONAUTO
25	10	DFE201612E-R33M=P2	Fixed IND SMD	Fixed IND 0.33uH 6300mA NONAUTO

26	10	DFE201612E-R47M=P2	Fixed IND SMD	Fixed IND 0.47uH 5500mA NONAUTO
27	10	DFE201612E-1R0M=P2	Fixed IND SMD	Fixed IND 1uH 4000mA NONAUTO
28	10	DFE201612E-1R5M=P2	Fixed IND SMD	Fixed IND 1.5uH 3200mA NONAUTO
29	10	DFE201612E-2R2M=P2	Fixed IND SMD	Fixed IND 2.2uH 2400mA NONAUTO
30	10	DFE201612E-4R7M=P2	Fixed IND SMD	Fixed IND 4.7uH 1800mA NONAUTO
31	10	DFE201610E-R24M=P2	Fixed IND SMD	Fixed IND 0.24uH 6300mA NONAUTO
32	10	DFE201610E-R33M=P2	Fixed IND SMD	Fixed IND 0.33uH 5500mA NONAUTO
33	10	DFE201610E-R47M=P2	Fixed IND SMD	Fixed IND 0.47uH 4800mA NONAUTO
34	10	DFE201610E-1R0M=P2	Fixed IND SMD	Fixed IND 1uH 3600mA NONAUTO
35	10	DFE201610E-1R5M=P2	Fixed IND SMD	Fixed IND 1.5uH 2900mA NONAUTO
36	10	DFE201610E-2R2M=P2	Fixed IND SMD	Fixed IND 2.2uH 2400mA NONAUTO
37	10	DFE201610E-4R7M=P2	Fixed IND SMD	Fixed IND 4.7uH 1600mA NONAUTO
38	10	DFE201610E-100M=P2	Fixed IND SMD	Fixed IND 10uH 1000mA NONAUTO
39	10	DFE21CCNR24MELL	Fixed IND SMD	Fixed IND 0.24uH 6500mA NONAUTO
40	10	DFE21CCNR47MELL	Fixed IND SMD	Fixed IND 0.47uH 4800mA NONAUTO
41	10	DFE21CCN1R0MELL	Fixed IND SMD	Fixed IND 1uH 3300mA NONAUTO
42	10	DFE21CCN2R2MELL	Fixed IND SMD	Fixed IND 2.2uH 2100mA NONAUTO