


FLASHNI

BEACON / SOUNDERS XENON



The Flashni is an audible and visual device which requires one single installation point. This greatly reduces installation and costs and is much less obtrusive than two separate devices. Versions are available with the sounder and beacon linked, or with separate terminals for independent operation.

- HIGH OUTPUT SOUNDER BEACON
- AUTOMATIC SOUNDER SYNCHRONISATION
- VOLUME CONTROL
- CHOICE OF LENS / SOUNDER COLOUR COMBINATIONS
- BASE COMPATIBLE WITH THE ROSHNI, CLARIFIRE AND IB BEACONS
- LOCKABLE BASE

Specification

Voltage	9 - 15Vdc @ 12V dc 18 - 30Vdc @ 24V dc
Current	100mA @ 12V dc 68mA @ 24V dc
Sound Output	101dB(A)
Monitoring	Reverse polarity
Beacon	0.7j
Flash Rate	60/min (1Hz)
Temperature	-10°C to +55°C
IP Rating	IP65
Weight	0.29Kg (Shallow Base) 0.33Kg (Deep / U Base)
Tones	12Vdc (preset to tone 5) 24Vdc (preset to tone 3)
Lens Colour	Red, Amber, Green, Blue or Clear
Body Colour	Red or White