


SQUASHNI MICRO PLATFORM



The Squashni Micro is an extremely efficient base sounder that offers ultra-low power operation. The sounder is available as either a standard version offering general UK alarm tones or an "E" version that provides European tones including the German DIN tone and the Netherlands Slow Whoop.

- FIXING PLATFORM FOR DETECTOR BASES
- LOW CURRENT CONSUMPTION
- BLANK COVER FOR USE AS A STAND ALONE SOUNDER
- REDUCED INSTALLATION COSTS
- TAMPER PROOF CAP

Specification

Voltage	9 - 30Vdc
Current	5.5mA at 24Vdc (lo setting) 15mA at 24Vdc (hi setting)
Sound Output	90dB(A) at 24Vdc (lo setting) 97dB(A) at 24Vdc (hi setting)
Temperature	- 25°C to + 70°C
Construction	ABS
IP Rating	IP23D
Weight	0.16Kg
Tones	4
Colours	Red or White (others available on request)