



Cordless - Screwdrivers - Inline Screwdrivers - 3.6 Volt Compact Cordless 3 Position Screwdriver

DC600KA



DC600KA Features

- A 3 position locking pivot operated from left or right and a gearbox diameter of only 40 mm for easy access to the tightest of working spaces with maximum user control
- Two speed control and 8 torque settings ideal for screwdriving applications and pilot drilling
- Pistol grip, soft grip handle and a rapid actuation switch for superior ergonomics and maximum user control in any working position
- Quick release 6.35 mm magnetic collet for ease of use and convenience
- All metal gearbox, metal gearcase and robust xenoy tool housing tough enough for the professional workplace
- Optimised working range in lower power applications upto 6 Nm for when it is a priority not to damage the screwhead or workpiece or where it is critical not to overtighten fixings
- LED light operated by an independent switch for visibility in tight working spaces

DC600KA Specifications

Voltage	3.6 V
Battery Capacity	NiCd 1.2 Ah
Tool Holder	(Hex) 6.35 mm
Power Output	n/a Watts
No Load Speed	200/600 rpm
Max Torque	6 Nm
Weight	0.7 kg
Length	300 mm
Height	65 mm

DC600KA Standard

- 1 hour charger
- 2 batteries
- Screwdriver bit
- Heavy duty carrying case