



## Saws - Jigsaws - Top Handle Jigsaw

DW341K



### DW341K Features

- Compact, ergonomic, design gives user comfort and versatility in use
- 550 Watt motor with large power reserves gives performance and durability
- Keyless blade change with patented anti-deflection clamp design for ease of use and accuracy
- Variable speed dial and trigger allows controlled cutting in all materials
- Adjustable pendulum action gives increased cutting performance and longer saw blade life
- Integrated sawdust blower gives a clear view of the cutting area
- Shoe bevels 45° to both left and right with presets at 0° and 45° for precise bevelled cuts
- Low profile dust extraction shield with bi-directional vacuum spout for clean, efficient cutting performance
- Heavy gauge steel shoe with anti-scratch coating and detachable anti-scratch shoe
- Can be used with a parallel guide or circular guide for accurate shape cutting
- Compatible with DEWALT flush cutting blade, DT2074 for cutting flush to an edge

### DW341K Specifications

Power Input	550 Watts
Power Output	350 Watts
No Load Stroke Rate	0-3100 spm
Stroke Length	20 mm
Bevel Capacity	45 °
Max. Cutting Capacity [Wood]	85 mm
Max. Cutting Capacity [Steel]	10 mm
Max. Cutting Capacity [Non Ferrous Metal]	20 mm
Weight	2.0 kg
Length	230 mm
Height	200 mm

### DW341K Standard

- Blade
- Allen key
- Anti-scratch shoe cover
- Dust extraction shield
- Vacuum adaptor
- Heavy duty carrying case