

Product image



Technical details

Description

NEW
Designation optional Basic for Metal

Areas of application

Metal plates [mm] 2,5-4
Pipes, profiles: closed [mm] <65
Aluminium [mm] <65

Details

Material HSS
Tooth design wavy set, milled
Length of teeth [mm] 106
Tooth spacing [mm] 2
Shank Single lug shank (T shank)
Application Wood with metal
Areas of application Medium-thick metal plates (2.5-6 mm), pipes +profiles inc. aluminium (diameter < 65 mm), precise angle cut
Type T 318 BF

Sales package qty: 5 Units
Despatch package qty:
1 Units
Bulk package quantity:
100 Units
Part No.: 2 608 631 404

PU: Packaging unit; PT: Packaging type; IPU: Interim packing unit; DPU: Despatch packaging unit; GPE: Masterpack