

Soldering Irons and Tips











Electronically Controlled Low Voltage Soldering Irons

The Weller soldering irons feature high precision and a very fast heat up time. The ergonomic design and high performance of the soldering irons allow fine soldering jobs as well as heavy duty tasks. A wide range of soldering tips makes them versatile for almost every job.



Order No.	Model	Description
005 29 101 99	MLR 21	Micro soldering iron 25 W, 24 V, with soldering tip MT H
005 15 019 99	KH 15	Safety rest

Soldering tips for MLR 21

Order No.	Model	Description	Width A	Length B
 005 44 105 99	MT 1S	Longform conical	ø 0,25 mm	-
 005 44 101 99	MT 1	Micropoint	0,25 mm	1,6 mm
 005 44 106 99	MT 6	Chisel slim	1,6 mm	0,4 mm
 005 44 112 99	MT H	Chisel	0,8 mm	0,4 mm
 005 44 110 99	MT A	Chisel	1,2 mm	0,4 mm
 005 44 111 99	MT B	Chisel	2,4 mm	0,4 mm
 005 44 113 99	MT HX	Chisel bent 45°	0,8 mm	0,4 mm
 005 44 104 99	MT 4	Sloped	ø 1,2 mm	
 005 44 119 99	MT GW	Gull wing	ø 2,0 mm	
 005 44 114 99		MT Measuring tip for thermo element ø 0,5 mm		

If any other tips are required, use LT tip series with MT / LT adapter

Order No./Model	Description
 005 44 121 99	MT-LT Adapter for use with LT series tips (see page 66 / 67)