

ABS case tape measure - 3 metres top reading with lock

893.316F

- 3 m x 16 mm matt, anti-glare, nylon-coated blade.
- Printed on both sides, for directly reading internal measurements in the window.
- Covering 2-rivet hook with stainless steel reinforcing plate.
- Ergonomic ABS case.
- Blister card presentation (145x96 mm).

	⊠	⊠	A	C x D	ΔΔ
	m	mm	mm	mm	g
893.316F	3	16	60	60 x 27	121



ABS case tape measure - 5 metres with lock

893.519

- 5 m x 19 mm matt, anti-glare, nylon-coated blade.
- Blade rigidity : 2.30 m vertically - 1.80 m horizontally.
- Covering 3-rivet hook with stainless steel reinforcing plate.
- Internal measurement obtained by adding dimension A (see table).
- Ergonomic ABS case.
- Blister card presentation (170x120 mm).

	⊠	⊠	A	C x D	ΔΔ
	m	mm	mm	mm	g
893.519	5	19	70	68 x 31	197



ABS case tape measure - 8 metres with lock

893.825

- 8 m x 25 mm matt, anti-glare, nylon-coated blade.
- Blade rigidity : 2.90 m vertically - 2.30 m horizontally.
- Covering 3-rivet hook with stainless steel reinforcing plate.
- Internal measurement obtained by adding dimension A (see table).
- Ergonomic ABS case.
- Blister card presentation (170x120 mm).

	⊠	⊠	A	C x D	ΔΔ
	m	mm	mm	mm	g
893.825	8	25	85	81,5 x 37,5	200



► Metal Case Series

800A-801A "Stainless" 2, 3 metres

- 2-rivet blade
- 16 mm wide, rigid up to 1.10m
- Compact.

	⊠	⊠	A	D x C	ΔΔ
	m	mm	mm	mm	g
800A	2	16	50	21,4 x 50	90
801A	3	16	60	21,4 x 60	125

