

# GP Batteries

**Data Sheet**


**Model No.: GP14G**

## NO MERCURY ADDED

Description : Mercury Free Extra Heavy Duty Battery, C Size  
 Chemical System : Zinc Chloride  
 Nominal Voltage : 1.5 Volts  
 Nominal Dimensions: Ø26.2 mm x 50.0 mm  
 Terminals : Protruded positive(+) and flat negative(-) contacts  
 Jacket : Metal jacket with PVC tube insulation  
 Applications : All electronic devices, e.g. transistor radios, cassette recorders, toys, alarm clocks, lighting & torches, portables fans.  
 Shelf Life : 24 months  
 Average Weight : 49g  
 Date Code : Unless otherwise specified, every battery will carry an expiry date code for 24 months. (e.g. a battery manufactured on January 1999 will carry an expiry code of 01-01.) 01 stands for January, 01 stands for 2001

### Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
3.9 Ohms	24 Hrs/ Day	0.9V	320 Mins



At 20°C within 30 days of manufacture

### Cross References:

GP	JIS	IEC	Eveready
14G	R14P	R14	1235

