

 1/4" "Radio" ratchets

Facom round head ratchets

 R.161
●○○○○○



 R.151
○○○○○●



 R.155A
●○○●○○




 R.157A
●●○○●○○



 R.158A
●●○○●○○



 R.150A
●○○●○○



 65.PE
○○●○○●●



The solution for congested spaces.

Compact :

- The Facom ratchet mechanism ensures a very compact round head design.

Precise :


- 72-tooth mechanism gives increments of only 5°

High performance :

- Meet the requirements of ISO 3315, DIN 3122 and NF ISO 3315.


Metal grip ratchets

- Ideal for environments where PVC grips are vulnerable to solvent attack.



Facom VSE 1000 V insulated ratchets



See the "VSE" series range of 1000 V insulated tools on page  662

