
## www.hammondmfg.com



## 154EA

## D.C. Reactors or Filter Chokes Low to Medium Current



## **Features**

- Economical "open bracket" channel mount.
- Tolerance of 15% on both inductance & resistance.
- Inductances measured at rated D.C. current.
- Minimum 5" long leads.
- Units will exhibit less inductance at slightly higher currents or more inductance at lower currents.
- Perfect for high voltage power supply filtering.
- Every unit is Hipot tested (100%) at 1,500 VAC
- Units are vacuum impregnated with polyurethane varnish for quiet and long life operation.

Mechanical	
А	2.06" / 52.3 mm
В	1.25" / 31.8 mm
С	1.19" / 30.2 mm
D	1.75" / 44.5 mm
G	0.19" / 4.8 mm
Weight	0.25 lbs / 0.11 kg
Electrical Electrical	
Inductance (+/- 15%)	15H
D.C. Current	20 ma.
Resistance (+/- 15%)	966 ohms
Maximum Operating Volt (D.C.)	300V