



DATA SHEET	53111600
SKINTOP® BS-M / BSR-M	valid from : 12.05.2006

SKINTOP® BS-M / BSR-M with polyamide spiral strain relief, is particularly used for flexible cables and handheld equipment, moving machine parts and in many applications of the instrument industry.
SKINTOP BS-M / BSR-M with spiral afford protection against conductor damage.



The gland component parts:

Gland body with lamellar design
Cap nut with spiral
Seal insert

plastic polyamide-based
plastic polyamide-based
elastomer

Technical features:

Connecting thread:
Functional thread:
IP protection:
Strain relief:
Temperature range:
Type:

M 12x1,5 up to M 32x1,5 in acc, to EN 60423
multi-start trapezoidal thread
IP 68 - 5 bar/ 30 min, test in accordance to EN 60 529
cat. A to EN 50262
- 20°C up to + 100°C by static strain
BS-M = standard
BSR-M = standard with reducing seal insert

Approval:



For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: R. Drotleff	Document: DB53111600_1EN	page 1 of 1
--------------------------------------	--------------------------	-------------