



- A range of high quality UK manufactured phono plugs made from machined brass with various plating options.
- Centre contact available in hollow tube.
 - Ground contact with unique 'T' shape slot for maximum contact area.
 - Internal cable clamp for secure cable connection.
 - Spring strain relief.
 - Colour coded ID rings for easy cable identification.
 - Attractive body styling.
 - Maximum cable size 5.5mm

Rating – 5A at 200 Vdc/150 Vac max.

Insulation resistance – 100M Ω at 500 Vdc

Dimensions



- Material
- Centre contact : Brass, silver plated
 - Ground contact : Brass, nickel plated
 - Insulation : Noryl SE1
 - Cable clamp : Brass, silver plated
 - Spring : Spring steel, nickel plated
 - Cap : Brass, nickel plated

Deltron Part No.	Description
330-0000	NICKEL PLATED
330-0100	NICKEL PLATED (BLACK ID RING)
330-0200	NICKEL PLATED (BLUE ID RING)
330-0500	NICKEL PLATED (RED ID RING)
330-0600	NICKEL PLATED (WHITE ID RING)
330-0700	NICKEL PLATED (YELLOW ID RING)

CONVERTED FROM PS0354 ISS2 (06.12.93) IN JAN 2003

Drgn No 330 SERIES TITLE THROUGH GROUNDED PHONO PLUG

ALL DIMENSIONS IN MM
ANGLES IN DECIMAL DEGREES



DELTRON Components

ISS 2

GENERAL SPECIFICATION
FOR 330 SERIES

CUSTOMER

FILTER REF

Aprvd Date 30/01/03

Aprvd By MC

Drwn by BS

Scale: NTS

Sheet 1 / 1