



Slip joint pliers, 221 D/225 D


DIN: 8976





ISO: 8976

Finish: phosphated, anti-rust protected, PVC-coated handles for better gripping comfort.

Shape: the jaws grip parallel in all positions up to maximum jaw opening.

IP = Industrial pack.



		 731415+		A mm	B mm	C mm	D mm	E mm	F mm	
221 D		0037070	5	117	16	18.0	5.0	3.0	5.0	18 60
222 D		0037087	5	150	22	23.5	6.5	4.0	6.5	23 100
223 D		0037094	5	192	25	28.0	7.5	4.5	7.5	32 185
224 D		0037100	5	240	30	35.0	9.5	5.5	9.5	45 345
225 D		0037117	3	305	38	42.0	11.5	4.5	11.5	58 535
221 D IP		0102334	5	117	16	18.0	5.0	3.0	5.0	18 60
222 D IP		0102341	5	150	22	23.5	6.5	4.0	6.5	23 100
223 D IP		0101788	5	192	25	28.0	7.5	4.5	7.5	32 185
224 D IP		0101795	5	240	30	35.0	9.5	5.5	9.5	45 345
225 D IP		0101801	5	305	38	42.0	11.5	4.5	11.5	58 535