



**Snipe nose pliers, 2430G ergo®**

Snipe nose plier with slim, semi-circular shaped and serrated jaws. Accurately machined jaws provide a sure grip on the workpiece. Equipped with return spring with on/off function. Tips give good grip and improved accessibility in confined spaces. Sharp edges for cutting softer material such as copper and plastic insulated wire.


ISO: 5745, DIN: 5745

**Finish:** Black oxidised, anti-corrosion treated.

**Material:** Chrome-Vanadium. With Ergo handles in two-material combination. Thermoplastic surface on tough polypropylene which gives a superior grip.

**Cutting capacity:** Hard steel wire.

**IP** = Industrial pack



	 731415+		<b>A</b> mm	<b>B</b> mm	<b>C</b> mm	<b>D E F G</b> mmmmmmmm	
2430 G-140	0102563	5	140	39	15	8 2.5 2.0 12 1.25 120	
2430 G-160	0024070	5	160	49	16	8 3.0 2.5 12 1.5 160	
2430 G-200	0100422	5	200	72	17	9 4.0 2.5 12 1.5 170	
2430 G-140 IP	0102143	5	140	39	15	8 2.5 2.0 12 1.25 120	
2430 G-160 IP	0100811	5	160	49	16	8 3.0 2.5 12 1.5 160	
2430 G-200 IP	0100835	5	200	72	17	9 4.0 2.5 12 1.5 170	