


I.D. PRO Plus®, Brady LS2000 and BradyMarker™ XC Plus Labels

PRINTER MODEL
PRO = ID PRO/PRO Plus
LS = LS2000
BMXC = BradyMarker XC Plus
ALL = All ID PRO, LS2000, BMXC



► **DURASLEEVE® WIRE MARKING INSERTS**

Polypropylene Inserts (B-389)

Part Number	Portable Printer Model	Inserts Per Roll	Insert Dimension Inch (mm)		Maximum Lines of Print	Maximum Characters Across Small
			A	B		
DMIDP-105-389	PRO	100	0.500 (12.70)	0.155 (3.93)	1	4
DMIDP-105-389-YL*	PRO	100	0.500 (12.70)	0.155 (3.93)	1	4
DMIDP-111-389	PRO	100	1.000 (25.40)	0.155 (3.93)	1	10
DMIDP-111-389-YL*	PRO	100	1.000 (25.40)	0.155 (3.93)	1	10
0.500" (12.70 mm) Insert Width						
DM-105-389	LS	500	0.500 (12.70)	0.155 (3.93)	1	7
DM-105-389-YL*	LS	500	0.500 (12.70)	0.155 (3.93)	1	7
1.000" (25.40 mm) Insert Width						
DM-111-389	LS	500	1.000 (25.40)	0.155 (3.93)	1	15
DM-111-389-YL*	LS	500	1.000 (25.40)	0.155 (3.93)	1	15
1.500" (38.10 mm) Insert Width						
DM-117-389	LS	500	1.500 (38.10)	0.155 (3.93)	1	23
DM-117-389-YL*	LS	500	1.500 (38.10)	0.155 (3.93)	1	23

*Yellow product is designated with a "YL" at the end of the part number.

► **DURASLEEVE® WIRE MARKING CARRIERS**

Part Number	Carrier Length Inches (mm)	Wire O.D. Inches (mm)	Type THHN Approximate Wire Gauge	Carriers per Box
DMC-1.3/3-15	0.590 (15.00)	0.051 (1.30) – 0.118 (3.00)	20 – 12	1000
DMC-1.3/3-30	1.180 (30.00)	0.051 (1.30) – 0.118 (3.00)	20 – 12	500
DMC-2.5/5-15	0.590 (15.00)	0.098 (2.50) – 0.197 (5.00)	16 – 10	1000
DMC-2.5/5-30	1.180 (30.00)	0.098 (2.50) – 0.197 (5.00)	16 – 10	500
DMC-4/10-15	0.590 (15.00)	0.157 (4.00) – 0.393 (10.00)	10 – 4	500
DMC-4/10-30	1.180 (30.00)	0.157 (4.00) – 0.393 (10.00)	10 – 4	200
DMC-8/16-15	0.590 (15.00)	0.315 (8.00) – 0.630 (16.00)	6 – 250	500
DMC-8/16-30	1.180 (30.00)	0.315 (8.00) – 0.630 (16.00)	6 – 250	200