


# Male to Stop End Bobbin Mounts

VE Series



Note: The Max. Working Load figure is per bobbin not the distributed load  
All dimensions are in mm, X = Amount the rubber is compressed when under the maximum working load

338563

D x H	V x I	°IRHD	Max. Working Load (kg)	X (mm)	Order Code
10x8	M4x10	45	9.5	2.0	<a href="#">499-7220</a>
10x8	M4x10	60	14.0	2.0	<a href="#">499-7232</a>
20x20	M6x18	60	39.0	5.0	<a href="#">499-7244</a>
25x15	M6x18	45	68.0	3.75	<a href="#">499-7256</a>
25x15	M6x18	60	104.0	3.75	<a href="#">499-7268</a>
25x20	M6x18	60	93.0	5.0	<a href="#">499-7270</a>
40x27	M8x23	60	184.5	6.75	<a href="#">499-7281</a>
40x35	M8x23	45	103.0	8.75	<a href="#">499-7293</a>
40x35	M10x25	60	153.5	8.75	<a href="#">499-7300</a>
50x21	M10x25	45	344.5	5.25	<a href="#">499-7311</a>
50x21	M10x25	60	514.0	5.25	<a href="#">499-7323</a>
50x30	M10x25	60	364.0	7.5	<a href="#">499-7335</a>
50x30	M10x25	80	607.0	7.5	<a href="#">499-7347</a>
75x30	M12x37	70	1807.0	7.5	<a href="#">499-7359</a>
100x50	M16x44	60	2022.0	12.5	<a href="#">499-7360</a>