


## ELECTRONICS PLIERS

## ▼ EXTENDED-NOSE PLIERS

**402.MT**


- ▷ ISO 9655  
 • For extra power.  
 ΔΔ: 76 g.



## ▼ RIGID LONG-NOSE PLIERS

**422.MT**


- ▷ ISO 9655  
 ΔΔ: 70 g.



## ▼ SHORT-NOSE PLIERS

**432.MT**


- ▷ ISO 9655  
 • Slim joint.  
 ΔΔ: 55 g.



## ▼ SNIPE-NOSE PLIERS

**432.LMT**

- ▷ ISO 9655  
 • Slim joint for precision work.  
 ΔΔ: 65 g.



## ▼ EXTENDED-NOSE 40° PLIERS

**403.MT**

- ▷ ISO 9655  
 • For extra power.  
 ΔΔ: 75 g.

